

3M™ Peltor™ Technical Datasheet



PELTOR™

Peltor™ WS™ ProTac XP, Ground Mechanic MT15H7AWS5-01 GB

Product description

The Peltor™ Ground Mechanic WS™ ProTac XP is an active-hearing hearing protector that features Bluetooth technology. The Bluetooth connection between headset and adapter ensures an efficient and safe push back. The headset provides effective noise attenuation when sound level is high.

Article number	3M ID number
MT15H7AWS5-01 GB	XH001679642

Key Features:

- DSP (Digital Noise Reduction)
- Supports Bluetooth A2DP profile for streaming high quality stereo sound
- VOX (Voice Operated Transmit)

Application:

The Peltor™ Ground Mechanic WS™ ProTac XP is designed to be used for Ground Mechanic Work at airports (push back and service).

Accessories:

Article number	3M ID number	Description
ACK051	XH001679642	Rechargeable Battery
FR05	XH001655469	Charger
FL6BA	XH001679956	Adapter cable for external PTT
M60/2	XH001652532	Wind Shield
HYM1000	XH001651328	Hygiene tape for boom mic



Testing and Approval:

MT15H7*WS5* is in conformity with the provisions set out in the PPE directive 89/686/EEC and the R&TTE directive 1999/5/EC. Thereby it fulfils the requirements for CE marking.

The product has been tested and approved in accordance with EN 352-1:2002, EN352-3:2002, EN352-4:2001, EN352- 6:2002, EN352- 8:2008, EN 60950-1:2006 +A1:2010 + A11:2009 + A12:2012, EN300 328 V1.7.1, EN 301 489-1 V1.8.1, EN 301 489-17 V2.1.1

The product has been examined by
Combitech AB, Kungsörsvägen 68, SE-732 81 Arboga, Sweden, Notified body #1914
Phoenix Testlab GmbH, Königswinkel 10, D-32825 Blomberg, Germany, Notified body #0700

3M™ Peltor™ Technical Datasheet

Technical Data Specifications:

Power: 2xAA NiMH or alkaline batteries, 2,4-3 V

Battery life time: Surround + Bluetooth (active) <24h , Surround only + Bluetooth off <150h

Bluetooth: This product supports Bluetooth version 2.1 headset, handsfree and A2DP profiles.

Other functions:

- The last settings are stored when the headset is switched off.
- Low battery level is indicated by a voice message: "low battery".
- Digital noise reduction on the boom microphone.

Weight: 396 g

Materials: Headband: Stainless steel with PVC covered head cushion, Cups: ABS

Storage: Recommended storage conditions: -20° C - +55° C, <90% humidity

Recommended maximum shelf life: 5 years except the batteries: <1 year

Use limitation: Never modify or alter this product

Warranty:

The warranty does not cover any damage caused by neglected maintenance or careless handling. For more information on maintenance, please see the user instruction.

For complete warranty condition, contact your dealer or local 3M office

Attenuation

MT15H7AWS5-01 GB

Frequency (Hz)	63	125	250	500	1000	2000	4000	8000
Mean attenuation (dB)	19,2	17,4	24,0	31,9	34,4	35,1	37,0	35,1
Std deviation (dB)	4,0	2,8	2,9	3,0	2,6	4,3	4,0	3,2
APV (84%)*	15,2	14,5	21,1	28,9	31,9	30,8	33,1	32,0

* Assumed Protection Value (dB)

SNR=31 db H=32 db M=29 db L=22 db

Important Notice:

3M does not accept liability of any kind, be it direct or consequential (including, but not limited to, loss of profits, business and/or goodwill) arising from reliance upon any information herein provided by 3M. The user is responsible for determining the suitability of the products for their intended use. Nothing in this statement will be deemed to exclude or restrict 3M's liability for death or personal injury arising from its negligence.



3M Occupational Health &
Environmental Safety Division
3M Svenska AB, Box 2341
SE-331 02 Värnamo
Sweden

Phone: +46 (0) 370 65 65 65

Fax: +46 (0) 370 65 65 99

Email: peltorcommunications@mmm.com

Internet: www.3M.com/Peltorcomms

Please recycle. Printed in Sweden.

© 3M 2012. All rights reserved.

Bluetooth is a registered trademark of Bluetooth SIG Inc